

Garant

Multi-part side panel, Usable depth 1350 mm, suitable for racking height: 2000mm

**Order data**

Order number	993260 2000
GTIN	4045197522023
Item class	91W

Description**Version:**

Sheet metal side panel consisting of plates fitted over each other. Supplied complete with fastenings.

Application:

For side closure of a rack (not suitable as divider between two racks). To enclose the left and right side of a complete racking bay 2 side panels (4-piece set) must be ordered.

Colour:

Light grey RAL 7035 **powder-coated**.

Technical description

suitable for racking height	2000 mm
Height	1875 mm
Application range	Heavy-duty racking
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	Usable depth 1350 mm
Width	1321 mm

Depth	2 mm
suitable for racking depth	1370 mm
Type of product	Side panel