

Garant

Roller shutter for basic rack, Usable depth 950 mm, suitable for racking height: 2500mm

**Order data**

Order number	993314 2500
GTIN	4045197613424
Item class	91W

Description**Version:**

Electrically-operated front-fitting roller shutter. Guide rails of extruded aluminium, shutter segments of rolled aluminium without light gaps. Lateral guide rails with paired brush seals. Electrical drive with radio-controlled motor and torque cut-out, with a single-channel hand-held radio remote control protected against splashed water. Automatic stop cut-out on encountering an obstacle.

Colour:

All frames light grey RAL 7035 powder-coated.

Technical description

suitable for racking height	2500 mm
Installation height	2685 mm
Article no of the battery / rechargeable battery fitted	081560 CR2430
Number of batteries contained	1

Application range	Special racking
Nominal voltage	250 V
Plug type, input	F
Product name attribute	Usable depth 950 mm
Width	1475 mm
Depth	105 mm
Type of product	Roller shutter