

Garant

Multi-part side panel, Usable depth 1350 mm, suitable for racking height: 2500mm

**Order data**

| | |
|--------------|---------------|
| Order number | 993260 2500 |
| GTIN | 4045197522030 |
| Item class | 91W |

Description**Version:**

Sheet metal side panel consisting of plates fitted over each other. Supplied complete with fastenings.

Application:

For side closure of a rack (not suitable as divider between two racks). To enclose the left and right side of a complete racking bay 2 side panels (5-piece set) must be ordered.

Colour:

Light grey RAL 7035 **powder-coated**.

Technical description

| | |
|-----------------------------|--|
| suitable for racking height | 2500 mm |
| Height | 2375 mm |
| Application range | Heavy-duty racking |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Product name attribute | Usable depth 1350 mm |
| Width | 1321 mm |

| | |
|----------------------------|------------|
| Depth | 2 mm |
| suitable for racking depth | 1370 mm |
| Type of product | Side panel |