

Garant

Bench vice with swivel base, Jaw width: 140mm



Order data

Order number	967120 140
GTIN	4045197612571
Item class	91J

Description

Version:

Entirely of forged steel – guaranteed unbreakable.

Slides forward on opening. With pipe clamping jaws underneath the normal jaws. Powerful, CNC-machined precision spindle with rolled thread. Spindle and guides are protected from dirt. Large hardened anvil area for shaping and upsetting work. Double adjustable guide. With solid, surface-hardened jaws (not interchangeable).

Advantage:

- **Tightening bar with impact-absorbing washers at both ends no irritating noise when the bar falls through.**
- **Long-pitch thread spindle for quick opening and closing.**
- **Interchangeable tightening bar.**
- **Opening scale embossed into slide.**

Supplied with:

Fasteners for attachment to the workbench.

Note:

For suitable height adjuster see No. 967520.

Technical description

Opening direction	opens to the front
Material	Drop forged steel

Jaw width	140 mm
exchangeable jaws	no
Type of product	Machinist's vice

Accessories

Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Bench vice mounting plate	967330
Swivel base separate suitable for vice size 140	967140 140
Clamping system with swing jaw Jaw width 140 mm	967150 140