

RIDGID
Peddinghaus**“Matador” bench vice, Jaw width: 100mm****Order data**

Order number	967170 100
GTIN	
Item class	93R

Description**Version:**

- Entirely of drop-forged steel - guaranteed unbreakable.
- Slides forward on opening; with two-pitch trapezoidal thread.
- Spindle protected from dirt.
- Milled, surface-hardened jaws.
- Hardened, adjustable guide.
- Measuring scale for quick pre-setting.
- Large hardened anvil area for shaping and upsetting work.

Sturdy design.

Callout:

Up to max. 90 mm

Supplied with:

Fasteners for attachment to the worktop.

Optional extras:

Additional jaw No. 967210; 967215; 967220; 967225, **from size 120 mm.**

Note:

For suitable height adjuster see No. 967530.

Technical description

Opening direction	opens to the front
-------------------	--------------------

Weight	6 kg
Jaw capacity	125 mm
Clamping depth	65 mm
Jaw width	100 mm
Series	Matador Multiplus
Type of product	Machinist's vice

Accessories

Pair of magnetic vice jawsAluminium, profiled Jaw width 100 mm	967722 100
Pair of light metal vice jaws with spring clips Jaw width 100 mm	967711 100
Pair of magnetic vice jawspolyurethane, serrated Jaw width 100 mm	967728 100
Pair of magnetic vice jawsAluminium / fibre cover, smooth Jaw width 100 mm	967724 100
Pair of magnetic vice jawsAluminium, Vee form Jaw width 100 mm	967723 100
Pair of magnetic vice jawsRubber, smooth Jaw width 100 mm	967727 100
Bench vice mounting plate	967330
Pair of magnetic vice jawsFelt, smooth Jaw width 100 mm	967726 100
Pair of magnetic vice jawspolyurethane, Vee form Jaw width 100 mm	967729 100
Pair of magnetic vice jawsAluminium, smooth, standard Jaw width 100 mm	967721 100
Bench vice mounting plate, bamboo Size 300X250	967328 300X250