

**Garant**

**Roller shutter for basic rack, Usable depth 1350 mm, suitable for racking height: 2500mm**

**Order data**

Order number	993310 2500
GTIN	4045197611789
Item class	91W

**Description****Version:**

Electrically-operated front-fitting roller shutter. Guide rails of extruded aluminium, shutter segments of rolled aluminium without light gaps. Lateral guide rails with paired brush seals. Electrical drive with radio-controlled motor and torque cut-out, with a single-channel hand-held radio remote control protected against splashed water. Automatic stop cut-out on encountering an obstacle.

**Colour:**

**All frames RAL 7035 light grey powder-coated.**

**Technical description**

Installation height	2685 mm
suitable for racking height	2500 mm
Article no of the battery / rechargeable battery fitted	081560 CR2430
Number of batteries contained	1

Application range	Special racking
Plug type, input	F
Nominal voltage	250 V
Product name attribute	Usable depth 1350 mm
Width	1075 mm
Depth	105 mm
Type of product	Roller shutter