



Pair of gloves KryTech 579, Glove size: 11



Order data

Order number	094465 11
GTIN	3245425791219
Item class	06D

Description

Version:

KryTech 579. For very delicate work in dry and less dirty working conditions. Good dexterity and very good sense of touch. **Breathable and sweat-absorbent material.**

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

EN 388 cut resistance	3
Accuracy of fit	good
Wet grip	medium
Heat protection	not available
silicone-free	yes
DMF-free	no

Glove size	11
EN 388 abrasion resistance	4
Breathability	good
Oil grip	medium
Material of coating	PU
EN 388 tear propagation resistance	4
Touch sensitivity	very good
EN 388 penetration resistance	3
Type of glove	Multi-purpose gloves
Protection category	Category II
Contents	96
Glove characteristics	free of latex
EN 388	4342B
Backing material	PEHD
Coating	PU
Coating variant	The palms of the hands
Application range	Precision
Colour	grey / white
Weight	25 g
Length	220 - 270 mm
Application	reusable
Cut protection class	B
Type of product	Cut-resistant gloves