

Garant

Bench vice with swivel base and interchangeable jaws, Jaw width: 140mm



Order data

| | |
|--------------|---------------|
| Order number | 967130 140 |
| GTIN | 4045197613745 |
| Item class | 91J |

Description

Version:

Entirely of forged steel – guaranteed unbreakable.

Slides forward on opening. With pipe clamping jaws underneath the normal jaws. Powerful, CNC-machined precision spindle with rolled thread. Spindle and guides are protected from dirt. Large hardened anvil area for shaping and upsetting work. Double adjustable guide. Replaceable jaws, surface-hardened. One side serrated, one side smooth (interchangeable).

Advantage:

- **Tightening bar with impact-absorbing washers at both ends no irritating noise when the bar falls through.**
- **Long-pitch thread spindle for quick opening and closing.**
- **Interchangeable tightening bar.**
- **Opening scale embossed into slide.**

Supplied with:

Fasteners for attachment to the workbench.

Note:

For suitable height adjuster see No. 967520.

Technical description

| | |
|-------------------|--------------------|
| Opening direction | opens to the front |
|-------------------|--------------------|

| | |
|-------------------|-------------------|
| Material | Drop forged steel |
| Jaw width | 140 mm |
| exchangeable jaws | yes |
| Type of product | Machinist's vice |

Accessories

| | |
|--|----------------|
| Swivel base separate suitable for vice size 140 | 967140 140 |
| Bench vice mounting plate, bamboo Size 300X250 | 967328 300X250 |
| Pair of spare jaws with screws for vice Jaw width 140 mm | 967145 140 |
| Bench vice mounting plate | 967330 |
| Clamping system with swing jaw Jaw width 140 mm | 967150 140 |