

RIDGID
 Peddinghaus

“Matador” bench vice, Jaw width: 120mm

Order data

Order number	967170 120
GTIN	
Item class	93R

Description
Version:

- Entirely of drop-forged steel - guaranteed unbreakable.
- Slides forward on opening; with two-pitch trapezoidal thread.
- Spindle protected from dirt.
- Milled, surface-hardened jaws.
- Hardened, adjustable guide.
- Measuring scale for quick pre-setting.
- Large hardened anvil area for shaping and upsetting work.

Sturdy design.

Callout:

Up to max. 90 mm

Supplied with:

Fasteners for attachment to the worktop.

Optional extras:

Additional jaw No. 967210; 967215; 967220; 967225, **from size 120 mm.**

Note:

For suitable height adjuster see No. 967530.

Technical description

Opening direction	opens to the front
-------------------	--------------------

Clamping depth	80 mm
Weight	10 kg
Jaw capacity	150 mm
Pipe jaws clamp pipes with outer Ø	1/8 – 4 in
Jaw width	120 mm
Series	Matador Multiplus
Type of product	Machinist's vice

Accessories

Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Pair of magnetic vice jaws Aluminium / fibre cover, smooth Jaw width 120 mm	967724 120
Bench vice mounting plate	967330
Pair of magnetic vice jaws Aluminium, profiled Jaw width 120 mm	967722 120
Pair of light metal vice jaws with spring clips Jaw width 120 mm	967711 120
Pair of magnetic vice jaws Aluminium, Vee form Jaw width 120 mm	967723 120