



## Pair of gloves ActivArmr Hycron® 27-607, Glove size: 8



### Order data

Order number	094430 8
GTIN	10076490102491
Item class	04P

### Description

#### Version:

ActivArmr Hycron® series. **Hard-wearing gloves** of jersey cotton with nitrile coating for the most demanding applications. High resistance to sharp-edged and chafing materials. Robust and more flexible than PVC, three times longer service life than heavy leather gloves. **Effective barrier against greases and oils.** Particularly suitable for rough castings, moulded plastic parts, steel bar, sheet metal, high-tensile cable, building materials, unfinished wood. With knitted cuffs and 3/4 coating for maintaining better breathability.

#### Standard:

EN 388; EN ISO 21420

Antistatisch gemäß EN 1149.

#### Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

### Technical description

Breathability	medium
Wet grip	good
DMF-free	no

Touch sensitivity	medium
Material of coating	Nitrile
Glove size	8
Accuracy of fit	good
silicone-free	yes
Heat protection	not available
Oil grip	good
Series	Hycron®
Type of glove	Multi-purpose gloves
Protection category	Category II
Contents	12
Glove characteristics	Silicone-free
Glove characteristics	free of latex
EN 388	4221X
Backing material	Cotton
Coating	Nitril
Coating variant	3/4 coating
Application range	Heavy Duty
Length	246 mm
Colour	blue
Weight	57 g
Application	reusable
Material	Nitrile
Type of product	Multi-purpose gloves