

RIDGID
 Peddinghaus

“Matador” bench vice, Jaw width: 140mm

Order data

Order number	967170 140
GTIN	
Item class	93R

Description
Version:

- Entirely of drop-forged steel - guaranteed unbreakable.
- Slides forward on opening; with two-pitch trapezoidal thread.
- Spindle protected from dirt.
- Milled, surface-hardened jaws.
- Hardened, adjustable guide.
- Measuring scale for quick pre-setting.
- Large hardened anvil area for shaping and upsetting work.

Sturdy design.

Callout:

Up to max. 90 mm

Supplied with:

Fasteners for attachment to the worktop.

Optional extras:

Additional jaw No. 967210; 967215; 967220; 967225, from size 120 mm.

Note:

For suitable height adjuster see No. 967530.

Technical description

Weight	18 kg
--------	-------

Opening direction	opens to the front
Clamping depth	95 mm
Jaw capacity	200 mm
Pipe jaws clamp pipes with outer Ø	1/8 – 5 in
Jaw width	140 mm
Series	Matador Multiplus
Type of product	Machinist's vice

Accessories

Pair of magnetic vice jaws Aluminium, Vee form Jaw width 140 mm	967723 140
Pair of magnetic vice jaws Aluminium / fibre cover, smooth Jaw width 140 mm	967724 140
Bench vice mounting plate	967330
Pair of magnetic vice jaws Aluminium, profiled Jaw width 140 mm	967722 140
Pipe jaw (one piece) for "Matador" Jaw width 140 mm	967210 140
Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Pair of light metal vice jaws with spring clips Jaw width 140 mm	967711 140