

**RIDGID**  
 Peddinghaus

**“Matador” bench vice with swivel base, Jaw width: 100 mm**

**Order data**

Order number	967180 100
GTIN	2050002047532
Item class	93R

**Description**
**Version:**

- Entirely of drop-forged steel - guaranteed unbreakable.
- Slides forward on opening; with two-pitch trapezoidal thread.
- Spindle protected from dirt.
- Milled, surface-hardened jaws.
- Hardened, adjustable guide.
- Measuring scale for quick pre-setting.
- Large hardened anvil area for shaping and upsetting work.

**With swivel base** for 360° rotation can be locked in any position by the clamping mechanism.

**Supplied with:**

Fasteners for attachment to the worktop.

**Optional extras:**

Additional jaw No. 967210; 967215; 967220; 967225, **from size 120 mm.**

Jaw capacity: 125 mm

Clamping depth: 65 mm

**Technical description**

Material	Drop forged steel
Opening direction	opens to the front

Clamping depth	65 mm
Jaw capacity	125 mm
Jaw width	100 mm
Series	Matador Multiplus
Type of product	Machinist's vice

## Accessories

Pair of magnetic vice jaws polyurethane, serrated Jaw width 100 mm	967728 100
Pair of magnetic vice jaws Felt, smooth Jaw width 100 mm	967726 100
Pair of magnetic vice jaws Aluminium, smooth, standard Jaw width 100 mm	967721 100
Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Pair of light metal vice jaws with spring clips Jaw width 100 mm	967711 100
Pair of magnetic vice jaws Aluminium, profiled Jaw width 100 mm	967722 100
Bench vice mounting plate	967330
Pair of magnetic vice jaws Rubber, smooth Jaw width 100 mm	967727 100
Pair of magnetic vice jaws polyurethane, Vee form Jaw width 100 mm	967729 100
Pair of magnetic vice jaws Aluminium, Vee form Jaw width 100 mm	967723 100
Pair of magnetic vice jaws Aluminium / fibre cover, smooth Jaw width 100 mm	967724 100
Swivel base separate suitable for vice size 100	967200 100