

RIDGID
 Peddinghaus

“Matador” bench vice with swivel base, Jaw width: 120 mm

Order data

Order number	967180 120
GTIN	2050002047549
Item class	93R

Description
Version:

- Entirely of drop-forged steel - guaranteed unbreakable.
- Slides forward on opening; with two-pitch trapezoidal thread.
- Spindle protected from dirt.
- Milled, surface-hardened jaws.
- Hardened, adjustable guide.
- Measuring scale for quick pre-setting.
- Large hardened anvil area for shaping and upsetting work.

With swivel base for 360° rotation can be locked in any position by the clamping mechanism.

Supplied with:

Fasteners for attachment to the worktop.

Optional extras:

Additional jaw No. 967210; 967215; 967220; 967225, **from size 120 mm.**

Jaw capacity: 150 mm

Clamping depth: 80 mm

Pipe jaws clamp pipes with outer Ø: 1/8 – 4 inch

Technical description

Jaw capacity	150 mm
--------------	--------

Clamping depth	80 mm
Material	Drop forged steel
Opening direction	opens to the front
Pipe jaws clamp pipes with outer Ø	1/8 – 4 inch
Jaw width	120 mm
Series	Matador Multiplus
Type of product	Machinist's vice

Accessories

Swivel base separate suitable for vice size 120	967200 120
Pipe jaw (one piece) for "Matador" Jaw width 120 mm	967210 120
Pair of steel jaws, smooth, for "Matador" Jaw width 120 mm	967215 120
Plastic soft jaws, smooth, for "Matador" Jaw width 120 mm	967220 120
Pair of Vee jaws for "Matador" Jaw width 120 mm	967225 120
Pair of magnetic vice jaws Aluminium / fibre cover, smooth Jaw width 120 mm	967724 120
Pair of magnetic vice jaws Aluminium, Vee form Jaw width 120 mm	967723 120
Pair of magnetic vice jaws Aluminium, profiled Jaw width 120 mm	967722 120
Pair of light metal vice jaws with spring clips Jaw width 120 mm	967711 120
Bench vice mounting plate	967330
Bench vice mounting plate, bamboo Size 300X250	967328 300X250