

**Bench vice, Jaw width: 175mm****Order data**

Order number	967260 175
GTIN	4045197694294
Item class	92H

Description**Version:**

Entirely of forged steel – guaranteed unbreakable.

Slides forward on opening. Milled, surface-hardened jaws. Large capacity. Strong lead screw with trapezoidal thread.

Lead screw and guides protected from dirt.

Adjustable guide; broad hardened anvil area.

Supplied with:

Fasteners for attachment to the workbench.

Optional extras:

Pipe jaws No. 967285.

Swivel base No. 967280, clamping plate No. 967290.

Note:

For suitable height adjuster see No. 967550.

Technical description

Opening direction	opens to the front
Jaw capacity	225 mm
Weight	24 kg
Material	Drop forged steel

Pipe jaws No. 967285 for clamping pipes with external Ø	1 – 5 in
Type of product	Machinist's vice

Accessories

Bench vice mounting plate	967330
Pair of pipe clamping jaws suitable for vice size 175	967285 175
Swivel base separate suitable for vice size 175	967280 175
Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Height adjuster for vice No. 967260 suitable for vice size 175	967550 175