

**Bench vice, Jaw width: 100mm****Order data**

Order number	967260 100
GTIN	4045197694263
Item class	92H

**Description****Version:**

**Entirely of forged steel – guaranteed unbreakable.**

**Slides forward on opening.** Milled, surface-hardened jaws. Large capacity. Strong lead screw with trapezoidal thread.

Lead screw and guides protected from dirt.

Adjustable guide; broad hardened anvil area.

**Supplied with:**

Fasteners for attachment to the workbench.

**Optional extras:**

Pipe jaws No. 967285.

Swivel base No. 967280, clamping plate No. 967290.

**Note:**

For suitable height adjuster see No. 967550.

**Technical description**

Pipe jaws No. 967285 for clamping pipes with external $\varnothing$	3/8 – 2.1/2 in
Material	Drop forged steel
Opening direction	opens to the front
Jaw capacity	125 mm

Weight	6 kg
Jaw width	100 mm
Type of product	Machinist's vice

## Accessories

Swivel base separate suitable for vice size 100	967280 100
Pair of light metal vice jaws with spring clips Jaw width 100 mm	967711 100
Pair of magnetic vice jawsAluminium, smooth, standard Jaw width 100 mm	967721 100
Pair of pipe clamping jaws suitable for vice size 100	967285 100
Bench vice mounting plate	967330
Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Pair of magnetic vice jawsRubber, smooth Jaw width 100 mm	967727 100
Pair of magnetic vice jawsAluminium, Vee form Jaw width 100 mm	967723 100
Pair of magnetic vice jawsFelt, smooth Jaw width 100 mm	967726 100
Bench clamp separately suitable for vice size 100	967290 100
Pair of magnetic vice jawspolyurethane, serrated Jaw width 100 mm	967728 100
Pair of magnetic vice jawsAluminium, profiled Jaw width 100 mm	967722 100
Pair of magnetic vice jawspolyurethane, Vee form Jaw width 100 mm	967729 100
Pair of magnetic vice jawsAluminium / fibre cover, smooth Jaw width 100 mm	967724 100