

**RIDGID**  
 Peddinghaus

**“Matador” bench vice with swivel base, Jaw width: 140 mm**

**Order data**

Order number	967180 140
GTIN	2050002047556
Item class	93R

**Description**
**Version:**

- Entirely of drop-forged steel - guaranteed unbreakable.
- Slides forward on opening; with two-pitch trapezoidal thread.
- Spindle protected from dirt.
- Milled, surface-hardened jaws.
- Hardened, adjustable guide.
- Measuring scale for quick pre-setting.
- Large hardened anvil area for shaping and upsetting work.

**With swivel base** for 360° rotation can be locked in any position by the clamping mechanism.

**Supplied with:**

Fasteners for attachment to the worktop.

**Optional extras:**

Additional jaw No. 967210; 967215; 967220; 967225, **from size 120 mm.**

Jaw capacity: 200 mm

Clamping depth: 95 mm

Pipe jaws clamp pipes with outer Ø: 1/8 – 5 inch

**Technical description**

Opening direction	opens to the front
-------------------	--------------------

Material	Drop forged steel
Jaw capacity	200 mm
Clamping depth	95 mm
Pipe jaws clamp pipes with outer Ø	1/8 – 5 inch
Jaw width	140 mm
Series	Matador Multiplus
Type of product	Machinist's vice

## Accessories

Swivel base separate suitable for vice size 140-180	967200 140-180
Pipe jaw (one piece) for "Matador" Jaw width 140 mm	967210 140
Pair of steel jaws, smooth, for "Matador" Jaw width 140 mm	967215 140
Plastic soft jaws, smooth, for "Matador" Jaw width 140 mm	967220 140
Pair of Vee jaws for "Matador" Jaw width 140 mm	967225 140
Pair of magnetic vice jaws Aluminium / fibre cover, smooth Jaw width 140 mm	967724 140
Pair of magnetic vice jaws Aluminium, Vee form Jaw width 140 mm	967723 140
Pair of magnetic vice jaws Aluminium, profiled Jaw width 140 mm	967722 140
Pair of light metal vice jaws with spring clips Jaw width 140 mm	967711 140
Bench vice mounting plate	967330
Bench vice mounting plate, bamboo Size 300X250	967328 300X250