


Garant**Clamping system with swing jaw, Jaw width: 140mm****Order data**

Order number	967150 140
GTIN	4045197612656
Item class	91J

Description**Version:**

Sturdy, cleanly machined jaws of high-quality aluminium alloy. Fixed jaw incorporates an integral magnetic strip. Swing jaw incorporates an extremely powerful cylindrical magnet.

Advantage:

No annoying slippage of the component, even under high clamping forces.

Application:

Unique clamping solution both for conical and asymmetrical components as well as for parallel-sided standard parts. Swivel angle up to 16°. Suitable for all vices with sufficient jaw width.

Technical description

Jaw width	140 mm
Material	Aluminium alloy
Type of fastening	Permanent magnet
Type of product	Vice jaws