

**Table / bench vice with bench clamp, Jaw width: 100mm****Order data**

Order number	967270 100
GTIN	4045197612724
Item class	92H

Description**Version:**

Entirely of forged steel – guaranteed unbreakable.

Slides forward on opening. Milled, surface-hardened jaws. Large capacity. Strong lead screw with trapezoidal thread.

Lead screw and guides protected from dirt.

Adjustable guide; broad hardened anvil area.

Application:

For clamping to the worktop.

Supplied with:

Fasteners for attachment to the workbench.

Optional extras:

Pipe jaws No. 967285.

Technical description

Weight	6.5 kg
Material	Drop forged steel
Opening direction	opens to the front
Clamping range	18 - 75 mm

Jaw capacity	125 mm
Pipe jaws No. 967285 for clamping pipes with external Ø	3/8 – 2.1/2 in
Jaw width	100 mm
Type of product	Machinist's vice

Accessories

Pair of light metal vice jaws with spring clips Jaw width 100 mm	967711 100
Pair of magnetic vice jaws polyurethane, Vee form Jaw width 100 mm	967729 100
Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Pair of magnetic vice jaws polyurethane, serrated Jaw width 100 mm	967728 100
Pair of magnetic vice jaws Aluminium / fibre cover, smooth Jaw width 100 mm	967724 100
Pair of magnetic vice jaws Aluminium, Vee form Jaw width 100 mm	967723 100
Bench vice mounting plate	967330
Pair of magnetic vice jaws Rubber, smooth Jaw width 100 mm	967727 100
Pair of magnetic vice jaws Aluminium, profiled Jaw width 100 mm	967722 100
Pair of pipe clamping jaws suitable for vice size 100	967285 100
Bench clamp separately suitable for vice size 100	967290 100
Pair of magnetic vice jaws Felt, smooth Jaw width 100 mm	967726 100
Pair of magnetic vice jaws Aluminium, smooth, standard Jaw width 100 mm	967721 100