

**RIDGID**  
 Peddinghaus

**“Matador” bench vice, Jaw width: 180 mm**

**Order data**

Order number	967170 180
GTIN	2050001780355
Item class	93R

**Description**
**Version:**

- Entirely of drop-forged steel - guaranteed unbreakable.
- Slides forward on opening; with two-pitch trapezoidal thread.
- Spindle protected from dirt.
- Milled, surface-hardened jaws.
- Hardened, adjustable guide.
- Measuring scale for quick pre-setting.
- Large hardened anvil area for shaping and upsetting work.

**Sturdy** design.

**Callout:**

Up to max. 90 mm

**Supplied with:**

Fasteners for attachment to the worktop.

**Optional extras:**

Additional jaw No. 967210; 967215; 967220; 967225, **from size 120 mm.**

**Note:**

For suitable height adjuster see No. 967530.

Jaw capacity: 225 mm

Clamping depth: 120 mm

Pipe jaws clamp pipes with outer Ø: 1/8 – 7 inch

Weight: 26 kg

## Technical description

Clamping depth	120 mm
Opening direction	opens to the front
Weight	26 kg
Jaw capacity	225 mm
Pipe jaws clamp pipes with outer Ø	1/8 – 7 inch
Jaw width	180 mm
Series	Matador Multiplus
Type of product	Machinist's vice

## Accessories

Height adjuster for vice No. 967170 suitable for vice size 160/180	967530 160/180
Swivel base separate suitable for vice size 140-180	967200 140-180
Pipe jaw (one piece) for "Matador" Jaw width 180 mm	967210 180
Bench vice mounting plate	967330
Bench vice mounting plate, bamboo Size 300X250	967328 300X250