

**RIDGID**  
 Peddinghaus

**“Matador” bench vice with swivel base, Jaw width: 180 mm**

**Order data**

Order number	967180 180
GTIN	2050002047570
Item class	93R

**Description**
**Version:**

- Entirely of drop-forged steel - guaranteed unbreakable.
- Slides forward on opening; with two-pitch trapezoidal thread.
- Spindle protected from dirt.
- Milled, surface-hardened jaws.
- Hardened, adjustable guide.
- Measuring scale for quick pre-setting.
- Large hardened anvil area for shaping and upsetting work.

**With swivel base** for 360° rotation can be locked in any position by the clamping mechanism.

**Supplied with:**

Fasteners for attachment to the worktop.

**Optional extras:**

Additional jaw No. 967210; 967215; 967220; 967225, **from size 120 mm.**

Jaw capacity: 225 mm

Clamping depth: 120 mm

Pipe jaws clamp pipes with outer Ø: 1/8 – 7 inch

**Technical description**

Clamping depth	120 mm
----------------	--------

Opening direction	opens to the front
Material	Drop forged steel
Jaw capacity	225 mm
Pipe jaws clamp pipes with outer Ø	1/8 – 7 inch
Jaw width	180 mm
Series	Matador Multiplus
Type of product	Machinist's vice

---

## Accessories

Swivel base separate suitable for vice size 140-180	967200 140-180
Pipe jaw (one piece) for "Matador" Jaw width 180 mm	967210 180
Bench vice mounting plate	967330
Bench vice mounting plate, bamboo Size 300X250	967328 300X250