

**Table / bench vice with bench clamp, Jaw width: 125mm****Order data**

Order number	967270 125
GTIN	4045197612731
Item class	92H

Description**Version:**

Entirely of forged steel – guaranteed unbreakable.

Slides forward on opening. Milled, surface-hardened jaws. Large capacity. Strong lead screw with trapezoidal thread.

Lead screw and guides protected from dirt.

Adjustable guide; broad hardened anvil area.

Application:

For clamping to the worktop.

Supplied with:

Fasteners for attachment to the workbench.

Optional extras:

Pipe jaws No. 967285.

Technical description

Material	Drop forged steel
Opening direction	opens to the front
Weight	10.5 kg
Clamping range	18 - 75 mm

Jaw capacity	150 mm
Pipe jaws No. 967285 for clamping pipes with external Ø	3/8 – 3 in
Jaw width	125 mm
Type of product	Machinist's vice

Accessories

Magnetic vice jaw set Jaw width 125 mm	967702 125
Bench vice mounting plate	967330
Pair of magnetic vice jawsAluminium, smooth, standard Jaw width 125 mm	967721 125
Bench clamp separately suitable for vice size 125	967290 125
Pair of magnetic vice jawspolyurethane, Vee form Jaw width 125 mm	967729 125
Pair of light metal vice jaws with spring clips Jaw width 125 mm	967711 125
Pair of magnetic vice jawsAluminium, profiled Jaw width 125 mm	967722 125
Pair of magnetic vice jawsAluminium / fibre cover, smooth Jaw width 125 mm	967724 125
Pair of pipe clamping jaws suitable for vice size 125	967285 125
Pair of magnetic vice jawsFelt, smooth Jaw width 125 mm	967726 125
Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Pair of magnetic vice jawsAluminium, Vee form Jaw width 125 mm	967723 125
Pair of magnetic vice jawspolyurethane, serrated Jaw width 125 mm	967728 125
Pair of magnetic vice jawsRubber, smooth Jaw width 125 mm	967727 125