

**Bench vice, Jaw width: 150mm****Order data**

Order number	967260 150
GTIN	4045197694287
Item class	92H

**Description****Version:**

**Entirely of forged steel – guaranteed unbreakable.**

**Slides forward on opening.** Milled, surface-hardened jaws. Large capacity. Strong lead screw with trapezoidal thread.

Lead screw and guides protected from dirt.

Adjustable guide; broad hardened anvil area.

**Supplied with:**

Fasteners for attachment to the workbench.

**Optional extras:**

Pipe jaws No. 967285.

Swivel base No. 967280, clamping plate No. 967290.

**Note:**

For suitable height adjuster see No. 967550.

**Technical description**

Weight	18 kg
Material	Drop forged steel
Pipe jaws No. 967285 for clamping pipes with external Ø	1 – 4 in
Opening direction	opens to the front

Jaw capacity	200 mm
Jaw width	150 mm
Type of product	Machinist's vice

## Accessories

Pair of magnetic vice jawsRubber, smooth Jaw width 150 mm	967727 150
Pair of magnetic vice jawsAluminium, smooth, standard Jaw width 150 mm	967721 150
Magnetic vice jaw set Jaw width 150 mm	967702 150
Bench vice mounting plate	967330
Height adjuster for vice No. 967260 suitable for vice size 150	967550 150
Pair of light metal vice jaws with spring clips Jaw width 150 mm	967711 150
Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Pair of magnetic vice jawsAluminium, Vee form Jaw width 150 mm	967723 150
Pair of magnetic vice jawspolyurethane, Vee form Jaw width 150 mm	967729 150
Pair of magnetic vice jawsAluminium / fibre cover, smooth Jaw width 150 mm	967724 150
Pair of magnetic vice jawsAluminium, profiled Jaw width 150 mm	967722 150
Pair of pipe clamping jaws suitable for vice size 150	967285 150
Pair of magnetic vice jawspolyurethane, serrated Jaw width 150 mm	967728 150
Swivel base separate suitable for vice size 150	967280 150
Pair of magnetic vice jawsFelt, smooth Jaw width 150 mm	967726 150