



Pair of gloves KryTech 563, Glove size: 8



Order data

Order number	094470 8
GTIN	3245425634189
Item class	04P

Description

Version:

KryTech 563. For **precision and general tasks** in dry and less dirty working environments. Excellent resistance to oils and greases. The abrasion-resistant nitrile coating ensures a long working life. Particularly suitable for grease guns of metal, dealing with sheet metal, mechanical maintenance work.

Standard:

EN 388; EN 420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Cut protection class: B

Colour: black / grey

silicone-free: yes

Technical description

Heat protection	not available
Accuracy of fit	very good
Weight	37 g

DMF-free	yes
EN 388 cut resistance	3
Glove size	8
Material of coating	Nitrile
Breathability	good
Oil grip	very good
EN 388 abrasion resistance	4
Touch sensitivity	very good
EN 388 tear propagation resistance	4
Wet grip	good
silicone-free	yes
EN 388 penetration resistance	3
Type of glove	Multi-purpose gloves
Protection category	Category II
EN 388:2016	4343B
Backing material	PEHD
Coating	Nitrile
Application range	All-round
Colour	black / grey
Cut protection class	B
Type of product	Cut-resistant gloves