

BROCKHAUS||HEUER

## “Heuer-Front” bench vice with swivel base, Jaw width: 140mm



### Order data

Order number	967370 140
GTIN	2050002047730
Item class	93Q

### Description

#### Version:

**Made entirely of forged steel – guaranteed unbreakable.**

**Opens forward.** With forged pipe jaws underneath the normal jaws. Strong spindle with **two-start trapezoidal thread** for quick opening and closing of the jaws. Galvanised spindle wrench with riveted steel circlips. Spindle and guide tracks protected from dirt. Adjustable, double-sided Vee guide.

With reinforced anvil shoulder for shaping and compressing work.

Serrated surface-hardened jaws, not interchangeable.

Swivel base can be rotated continuously 360° and can be securely locked in any position.

#### Supplied with:

Fastening screws for attachment to the worktop.

#### Colour:

Hammer-effect blue, **powder-coated.**

### Technical description

Opening direction	opens to the front
Material	Drop forged steel
Jaw width	140 mm
Series	Heuer Front
exchangeable jaws	no

Type of product	Machinist's vice
-----------------	------------------

## Accessories

Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Bench vice mounting plate	967330
Pair of light metal vice jaws with spring clips Jaw width 140 mm	967711 140
Pair of magnetic vice jaws Aluminium, profiled Jaw width 140 mm	967722 140
Pair of magnetic vice jaws Aluminium, Vee form Jaw width 140 mm	967723 140
Pair of magnetic vice jaws Aluminium / fibre cover, smooth Jaw width 140 mm	967724 140
Swivel base separate suitable for vice size 140/1	967390 140/1
10X50/3	967002 10X50/3
"Heuer-Front" bench vice Jaw width 140/1 mm	967350 140/1
10X50/4	967002 10X50/4