

BROCKHAUS | HEUER

“Heuer-Front” bench vice, Jaw width: 180mm**Order data**

Order number	967350 180
GTIN	2050002047679
Item class	93Q

Description**Version:****Made entirely of forged steel – guaranteed unbreakable.****Opens forward.** With forged pipe jaws underneath the normal jaws. Strong spindle with **two-start trapezoidal thread** for quick opening and closing of the jaws. Galvanised spindle wrench with riveted steel circlips. Spindle and guide tracks protected from dirt. Adjustable, double-sided Vee guide.

With reinforced anvil shoulder for shaping and compressing work.

Serrated surface-hardened jaws, not interchangeable.

Supplied with:

Fastening screws for attachment to the worktop.

Colour:Hammer-effect blue, **powder-coated.****Note:**

For suitable height adjuster see No. 967540.

Technical description

Clamping depth	100 mm
Opening direction	opens to the front
Weight	29 kg
Material	Drop forged steel

Jaw capacity	225 mm
Pipe jaws clamp pipes with outer Ø	27 - 100 mm
Jaw width	180 mm
Series	Heuer Front
exchangeable jaws	no
Type of product	Machinist's vice

Accessories

Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Swivel base separate suitable for vice size 160/180	967390 160/180
Height adjuster for vices No. 967350 / 7360 / 7420 / 7430 suitable for vice size 160/180	967540 160/180
Bench vice mounting plate	967330