

BROCKHAUS | HEUER

“Heuer-Front” bench vice, Jaw width: 100mm**Order data**

Order number	967350 100
GTIN	2050002047631
Item class	93Q

Description**Version:****Made entirely of forged steel – guaranteed unbreakable.****Opens forward.** With forged pipe jaws underneath the normal jaws. Strong spindle with **two-start trapezoidal thread** for quick opening and closing of the jaws. Galvanised spindle wrench with riveted steel circlips. Spindle and guide tracks protected from dirt. Adjustable, double-sided Vee guide.

With reinforced anvil shoulder for shaping and compressing work.

Serrated surface-hardened jaws, not interchangeable.

Supplied with:

Fastening screws for attachment to the worktop.

Colour:Hammer-effect blue, **powder-coated**.**Note:**

For suitable height adjuster see No. 967540.

Technical description

Jaw capacity	125 mm
Weight	4.5 kg
Opening direction	opens to the front
Material	Drop forged steel

Clamping depth	50 mm
Pipe jaws clamp pipes with outer Ø	16 - 30 mm
Jaw width	100 mm
Series	Heuer Front
exchangeable jaws	no
Type of product	Machinist's vice

Accessories

Pair of magnetic vice jaws Felt, smooth Jaw width 100 mm	967726 100
Pair of magnetic vice jaws polyurethane, serrated Jaw width 100 mm	967728 100
Pair of light metal vice jaws with spring clips Jaw width 100 mm	967711 100
Swivel base separate suitable for vice size 100	967390 100
Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Bench clamp separately For vice "Heuer-Front" size 100	967400 100
Pair of magnetic vice jaws Aluminium, profiled Jaw width 100 mm	967722 100
Pair of magnetic vice jaws Aluminium, smooth, standard Jaw width 100 mm	967721 100
Bench vice mounting plate	967330
Pair of magnetic vice jaws Rubber, smooth Jaw width 100 mm	967727 100
Pair of magnetic vice jaws polyurethane, Vee form Jaw width 100 mm	967729 100
Pair of magnetic vice jaws Aluminium, Vee form Jaw width 100 mm	967723 100
Pair of magnetic vice jaws Aluminium / fibre cover, smooth Jaw width 100 mm	967724 100