

**Bench vice, Jaw width: 120mm****Order data**

Order number	967420 120
GTIN	4045197694362
Item class	92H

Description**Version:**

Entirely of steel – guaranteed unbreakable. Slides forward on opening. With forged pipe clamping jaws underneath the normal jaws. Lead screw with trapezoidal thread, enclosed and protected from dirt. Double Vee form guide with adjustment facility. With anvil shoulder for light shaping and upsetting.

With serrated, hardened jaws (not exchangeable).

Supplied with:

Fasteners for attachment to the workbench.

Note:

For suitable height adjuster see No. 967540.

Technical description

Clamping depth	65 mm
Jaw capacity	120 mm
Weight	9 kg
Material	Drop forged steel
Opening direction	opens to the front
Pipe jaws clamp pipes with outer Ø	20 - 55 mm

Jaw width	120 mm
exchangeable jaws	no
Type of product	Machinist's vice

Accessories

Pair of magnetic vice jaws Aluminium / fibre cover, smooth Jaw width 120 mm	967724 120
Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Height adjuster for vices No. 967350 / 7360 / 7420 / 7430 suitable for vice size 120	967540 120
Pair of magnetic vice jaws Aluminium, Vee form Jaw width 120 mm	967723 120
Bench vice mounting plate	967330
Pair of light metal vice jaws with spring clips Jaw width 120 mm	967711 120
Pair of magnetic vice jaws Aluminium, profiled Jaw width 120 mm	967722 120