

BROCKHAUS | HEUER

“Heuer-Front” bench vice with interchangeable jaws, Jaw width: 120mm



Order data

Order number	967360 120
GTIN	2050002047686
Item class	93Q

Description

Version:

Made entirely of forged steel – guaranteed unbreakable.

Opens forward. With forged pipe jaws underneath the normal jaws. Strong spindle with **two-start trapezoidal thread** for quick opening and closing of the jaws. Galvanised spindle wrench with riveted steel circlips. Spindle and guide tracks protected from dirt. Adjustable, double-sided Vee guide.

With reinforced anvil shoulder for shaping and compressing work.

Replaceable jaws, surface-hardened. One side **serrated**, one side **smooth**. Reversible and interchangeable.

Supplied with:

Fastening screws for attachment to the worktop.

Colour:

Hammer-effect blue, **powder-coated**.

Note:

For suitable height adjuster see No. 967540.

Technical description

Opening direction	opens to the front
Jaw capacity	150 mm
Clamping depth	65 mm

Weight	9 kg
Material	Drop forged steel
Pipe jaws clamp pipes with outer Ø	16 - 55 mm
Jaw width	120 mm
Series	Heuer Front
exchangeable jaws	no
Type of product	Machinist's vice

Accessories

Height adjuster for vices No. 967350 / 7360 / 7420 / 7430 suitable for vice size 120	967540 120
Pair of magnetic vice jaws Aluminium / fibre cover, smooth Jaw width 120 mm	967724 120
Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Pair of light metal vice jaws with spring clips Jaw width 120 mm	967711 120
Swivel base separate suitable for vice size 120	967390 120
Pair of spare jaws with screws for "Heuer Front" Jaw width 120 mm	967405 120
Bench vice mounting plate	967330
Pair of magnetic vice jaws Aluminium, profiled Jaw width 120 mm	967722 120
Pair of magnetic vice jaws Aluminium, Vee form Jaw width 120 mm	967723 120