

BROCKHAUS | HEUER

“Heuer-Front” bench vice, Jaw width: 120mm**Order data**

Order number	967350 120
GTIN	2050002047648
Item class	93Q

Description**Version:****Made entirely of forged steel – guaranteed unbreakable.****Opens forward.** With forged pipe jaws underneath the normal jaws. Strong spindle with **two-start trapezoidal thread** for quick opening and closing of the jaws. Galvanised spindle wrench with riveted steel circlips. Spindle and guide tracks protected from dirt. Adjustable, double-sided Vee guide.

With reinforced anvil shoulder for shaping and compressing work.

Serrated surface-hardened jaws, not interchangeable.

Supplied with:

Fastening screws for attachment to the worktop.

Colour:Hammer-effect blue, **powder-coated.****Note:**

For suitable height adjuster see No. 967540.

Technical description

Clamping depth	65 mm
Material	Drop forged steel
Opening direction	opens to the front
Jaw capacity	150 mm

Weight	9 kg
Pipe jaws clamp pipes with outer Ø	16 - 55 mm
Jaw width	120 mm
Series	Heuer Front
exchangeable jaws	no
Type of product	Machinist's vice

Accessories

Bench vice mounting plate	967330
Pair of magnetic vice jaws Aluminium / fibre cover, smooth Jaw width 120 mm	967724 120
Pair of magnetic vice jaws Aluminium, profiled Jaw width 120 mm	967722 120
Pair of magnetic vice jaws Aluminium, Vee form Jaw width 120 mm	967723 120
Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Height adjuster for vices No. 967350 / 7360 / 7420 / 7430 suitable for vice size 120	967540 120
Pair of light metal vice jaws with spring clips Jaw width 120 mm	967711 120
Swivel base separate suitable for vice size 120	967390 120