

**Bench vice, Jaw width: 140mm****Order data**

Order number	967420 140
GTIN	4045197694379
Item class	92H

Description**Version:**

Entirely of steel – guaranteed unbreakable. Slides forward on opening. With forged pipe clamping jaws underneath the normal jaws. Lead screw with trapezoidal thread, enclosed and protected from dirt. Double Vee form guide with adjustment facility. With anvil shoulder for light shaping and upsetting.

With serrated, hardened jaws (not exchangeable).

Supplied with:

Fasteners for attachment to the workbench.

Note:

For suitable height adjuster see No. 967540.

Technical description

Weight	16 kg
Jaw capacity	180 mm
Material	Drop forged steel
Clamping depth	90 mm
Opening direction	opens to the front
Pipe jaws clamp pipes with outer Ø	20 - 80 mm

Jaw width	140 mm
exchangeable jaws	no
Type of product	Machinist's vice

Accessories

Bench vice mounting plate	967330
Height adjuster for vices No. 967350 / 7360 / 7420 / 7430 suitable for vice size 140	967540 140
Pair of magnetic vice jaws Aluminium, profiled Jaw width 140 mm	967722 140
Pair of light metal vice jaws with spring clips Jaw width 140 mm	967711 140
Pair of magnetic vice jaws Aluminium / fibre cover, smooth Jaw width 140 mm	967724 140
Pair of magnetic vice jaws Aluminium, Vee form Jaw width 140 mm	967723 140
Bench vice mounting plate, bamboo Size 300X250	967328 300X250