

BROCKHAUS  HEUER**“Heuer-Front” bench vice with interchangeable jaws, Jaw width: 140mm****Order data**

Order number	967360 140
GTIN	2050002047693
Item class	93Q

Description**Version:****Entirely forged of steel - guaranteed unbreakable.**

Slides forward on opening. With forged pipe jaws underneath the normal jaws. Strong, fully galvanised spindle with **two-start trapezoidal thread** for quick opening and closing of the jaws. Galvanised spindle wrench with steel circlips. Spindle and guides protected from dirt. Adjustable, double-sided Vee guide.

With reinforced anvil shoulder for shaping and upsetting work.

Jaws used surface-hardened and galvanised. One side **serrated**, one side **smooth**. Reversible and interchangeable.

Supplied with:

Fastening screws for attachment to the worktop.

Colour:

Hammer-effect blue, **powder-coated**.

Note:

For suitable height adjuster see No. 967540.

Technical description

Jaw capacity	200 mm
Opening direction	opens to the front
Clamping depth	80 mm

Data sheet

Weight	16 kg
Material	Drop forged steel
Pipe jaws clamp pipes with outer Ø	27 - 70 mm
Jaw width	140 mm
Series	Heuer Front
exchangeable jaws	no
Type of product	Machinist's vice

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/967360-140>