

BROCKHAUS | HEUER

“Heuer-Front” bench vice with interchangeable jaws, Jaw width: 140mm



Order data

Order number	967360 140
GTIN	2050002047693
Item class	93Q

Description

Version:

Made entirely of forged steel – guaranteed unbreakable.

Opens forward. With forged pipe jaws underneath the normal jaws. Strong spindle with **two-start trapezoidal thread** for quick opening and closing of the jaws. Galvanised spindle wrench with riveted steel circlips. Spindle and guide tracks protected from dirt. Adjustable, double-sided Vee guide.

With reinforced anvil shoulder for shaping and compressing work.

Replaceable jaws, surface-hardened. One side **serrated**, one side **smooth**. Reversible and interchangeable.

Supplied with:

Fastening screws for attachment to the worktop.

Colour:

Hammer-effect blue, **powder-coated**.

Note:

For suitable height adjuster see No. 967540.

Technical description

Jaw capacity	200 mm
Opening direction	opens to the front
Clamping depth	80 mm

Weight	16 kg
Material	Drop forged steel
Pipe jaws clamp pipes with outer Ø	27 - 70 mm
Jaw width	140 mm
Series	Heuer Front
exchangeable jaws	no
Type of product	Machinist's vice

Accessories

Pair of magnetic vice jaws Aluminium / fibre cover, smooth Jaw width 140 mm	967724 140
Pair of spare jaws with screws for "Heuer Front" Jaw width 140 mm	967405 140
Bench vice mounting plate	967330
Pair of magnetic vice jaws Aluminium, profiled Jaw width 140 mm	967722 140
Pair of light metal vice jaws with spring clips Jaw width 140 mm	967711 140
Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Swivel base separate suitable for vice size 140	967390 140
Height adjuster for vices No. 967350 / 7360 / 7420 / 7430 suitable for vice size 140	967540 140
Pair of magnetic vice jaws Aluminium, Vee form Jaw width 140 mm	967723 140