

Garant**Height adjuster for vice No. 967000, suitable for vice size: 100****Order data**

Order number	967500 100
GTIN	4045197694423
Item class	91J

Description**Version:**

Sturdy and very strong **forged parts** / steel design. Very smooth-running and precise guidance due to CNC-machined components. Extremely strong clamping by the special locking device. A built-in gas pressure spring ensures weight compensation during height adjustment of the vice. Quick clamping in any desired position by means of the **safety clamping lever**.

Advantage:

In conjunction with the height adjuster the vice can be **rotated by 360° without an additional swivel base** in order to bring the component into the best working position. The safety margin of 25 mm specified in DIN 31001 part 1 is kept during all height and angle adjustments.

Application:

For centimetre-accurate adjustment of the vice to the ideal working height (particularly important in training workshops and school workshops).

Suitable for:

Bench vice GARANT No. 967000.

Supplied with:

All fastening screws for attachment to the workbench.

Colour:

Silver-grey.

Note:

Height adjustment unit also suitable for original LEINEN vices (not LEINEN-JUNIOR No. 967060).

Technical description

Height adjustment range	242 mm
adjustable above workbench top	93 - 335 mm
Weight	11.8 kg
suitable for vice size	100
Type of product	Height adjuster