

Garant

eco grooving tool strengthened, right-hand, Blade height h₅ / groove width w: 32/3mm



Order data

Order number	273864 32/3
GTIN	4045197983541
Item class	21W

Description

Version:

With eco cooling directly to the cutting edge and additional rake face cooling.

Suitable for:

Toolholder No. 273893; 273894; 274095; 274097 or VDI toolholder 319133.

Attention:

Please order the assembly key No. 279920 separately.

Note:

Due to its design, it is not compatible with EWS toolholders No. 319148 and 319149.

Technical description

Blade height h ₅	32 mm
Groove width w	3 mm
Height h ₁	25 mm
Series	Eco
for maximum workpiece Ø	65 mm
Overall length L	109.5 mm
Application type	right-hand
Through-coolant	yes
axial grooving possible	no

Type of product

Parting-off tool