

BROCKHAUS | HEUER

**“Heuer-Front” bench vice with bench clamp, Jaw width: 100mm****Order data**

Order number	967395 100
GTIN	2050002047839
Item class	93Q

**Description****Version:**

**Made entirely of forged steel – guaranteed unbreakable.**

**Opens forward.** With forged pipe jaws underneath the normal jaws. Strong spindle with **two-start trapezoidal thread** for quick opening and closing of the jaws. Galvanised spindle wrench with riveted steel circlips. Spindle and guide tracks protected from dirt. Adjustable, double-sided Vee guide.

With reinforced anvil shoulder for shaping and compressing work.

Serrated surface-hardened jaws, not interchangeable.

Bench clamp for worktops of 10 – 60 mm thickness.

**Application:**

For clamping to the worktop.

**Colour:**

Hammer-effect blue, **powder-coated.**

**Technical description**

Weight	5 kg
Opening direction	opens to the front

Clamping range	10 - 60 mm
Material	Drop forged steel
Pipe jaws clamp pipes with outer Ø	3/8 – 1 in
Jaw width	100 mm
Series	Heuer Front
Type of product	Machinist's vice

## Accessories

Pair of light metal vice jaws with spring clips Jaw width 100 mm	967711 100
Pair of magnetic vice jawsAluminium, Vee form Jaw width 100 mm	967723 100
Pair of magnetic vice jawsAluminium / fibre cover, smooth Jaw width 100 mm	967724 100
Pair of magnetic vice jawsFelt, smooth Jaw width 100 mm	967726 100
Pair of magnetic vice jawspolyurethane, Vee form Jaw width 100 mm	967729 100
Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Pair of magnetic vice jawsAluminium, profiled Jaw width 100 mm	967722 100
Pair of magnetic vice jawsAluminium, smooth, standard Jaw width 100 mm	967721 100
Pair of magnetic vice jawspolyurethane, serrated Jaw width 100 mm	967728 100
Bench vice mounting plate	967330
Pair of magnetic vice jawsRubber, smooth Jaw width 100 mm	967727 100
Bench clamp separately For vice "Heuer-Front" size 100	967400 100