

BROCKHAUS||HEUER

“Heuer-Front” bench vice with interchangeable jaws, Jaw width: 160mm**Order data**

Order number	967360 160
GTIN	2050002047709
Item class	93Q

Description**Version:**

Made entirely of forged steel – guaranteed unbreakable.

Opens forward. With forged pipe jaws underneath the normal jaws. Strong spindle with **two-start trapezoidal thread** for quick opening and closing of the jaws. Galvanised spindle wrench with riveted steel circlips. Spindle and guide tracks protected from dirt. Adjustable, double-sided Vee guide.

With reinforced anvil shoulder for shaping and compressing work.

Replaceable jaws, surface-hardened. One side **serrated**, one side **smooth**. Reversible and interchangeable.

Supplied with:

Fastening screws for attachment to the worktop.

Colour:

Hammer-effect blue, **powder-coated**.

Note:

For suitable height adjuster see No. 967540.

Technical description

Material	Drop forged steel
Jaw capacity	225 mm
Clamping depth	100 mm

Opening direction	opens to the front
Weight	27 kg
Pipe jaws clamp pipes with outer Ø	27 - 100 mm
Jaw width	160 mm
Series	Heuer Front
exchangeable jaws	no
Type of product	Machinist's vice

Accessories

Pair of magnetic vice jaws Aluminium / fibre cover, smooth Jaw width 160 mm	967724 160
Bench vice mounting plate	967330
Pair of magnetic vice jaws Aluminium, profiled Jaw width 160 mm	967722 160
Pair of spare jaws with screws for "Heuer Front" Jaw width 160 mm	967405 160
Swivel base separate suitable for vice size 160/180	967390 160/180
Pair of magnetic vice jaws Aluminium, Vee form Jaw width 160 mm	967723 160
Height adjuster for vices No. 967350 / 7360 / 7420 / 7430 suitable for vice size 160/180	967540 160/180
Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Pair of light metal vice jaws with spring clips Jaw width 160 mm	967711 160