

HOLEX**Bench vice, Jaw width: 160mm****Order data**

| | |
|--------------|---------------|
| Order number | 967420 160 |
| GTIN | 4045197694386 |
| Item class | 92H |

Description**Version:**

Entirely of steel – guaranteed unbreakable. Slides forward on opening. With forged pipe clamping jaws underneath the normal jaws. Lead screw with trapezoidal thread, enclosed and protected from dirt. Double Vee form guide with adjustment facility. With anvil shoulder for light shaping and upsetting.

With serrated, hardened jaws (not exchangeable).

Supplied with:

Fasteners for attachment to the workbench.

Note:

For suitable height adjuster see No. 967540.

Technical description

| | |
|------------------------------------|--------------------|
| Weight | 27 kg |
| Opening direction | opens to the front |
| Material | Drop forged steel |
| Clamping depth | 100 mm |
| Jaw capacity | 210 mm |
| Pipe jaws clamp pipes with outer Ø | 25 - 100 mm |

| | |
|-------------------|------------------|
| Jaw width | 160 mm |
| exchangeable jaws | no |
| Type of product | Machinist's vice |

Accessories

| | |
|--|----------------|
| Pair of magnetic vice jawsAluminium, Vee form Jaw width 160 mm | 967723 160 |
| Bench vice mounting plate, bamboo Size 300X250 | 967328 300X250 |
| Pair of light metal vice jaws with spring clips Jaw width 160 mm | 967711 160 |
| Pair of magnetic vice jawsAluminium / fibre cover, smooth Jaw width 160 mm | 967724 160 |
| Bench vice mounting plate | 967330 |
| Pair of magnetic vice jawsAluminium, profiled Jaw width 160 mm | 967722 160 |
| Height adjuster for vices No. 967350 / 7360 / 7420 / 7430 suitable for vice size 160/180 | 967540 160/180 |