

BROCKHAUS | HEUER

"Heuer-Compact" bench vice with quick adjustment, Jaw width: 120 mm**Order data**

Order number	967460 120
GTIN	2050002047846
Item class	93Q

Description**Version:**

Lightweight, steel with compact dimensions, **entirely forged of steel. Opens forwards.**

With integral pipe jaws underneath the normal jaws.

New type of **quick adjustment of the jaw opening** from 0 to 130 mm simply by twisting the pipe body and pulling out the front jaw directly.

Additional jaw opening indications on the tubular body with centimetre graduations to simplify pre-setting.

Jaws used surface-hardened and galvanised. Clamping force 10 kN.

One side **serrated**, one side **smooth**. Reversible and interchangeable.

Callout:

Twist release.

Quick adjustment of jaw opening.

Supplied with:

Fasteners for attachment to the workbench.

Optional extras:

Swivel base No. 967390 **size 100.**

Spare jaws No. 967405 size 120.

Bench clamp No. 967400 size 100.

Jaw capacity: 130 mm

Clamping depth: 65 mm

Pipe jaws clamp pipes with outer Ø: 15 - 50 mm

Weight: 4.5 kg

Technical description

Jaw capacity	130 mm
Clamping capacity quick adjustment	yes
Material	Forged steel
Weight	4.5 kg
Clamping depth	65 mm
Opening direction	opens to the front
Pipe jaws clamp pipes with outer Ø	15 - 50 mm
Jaw width	120 mm
Series	Heuer Compact
exchangeable jaws	yes
Type of product	Machinist's vice

Accessories

Pair of magnetic vice jaws Aluminium, Vee form Jaw width 120 mm	967723 120
Swivel base separate suitable for vice size 100	967390 100
Pair of magnetic vice jaws Aluminium, profiled Jaw width 120 mm	967722 120
Bench vice mounting plate	967330
Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Bench clamp separately For vice "Heuer-Front" size 100	967400 100
Pair of light metal vice jaws with spring clips Jaw width 120 mm	967711 120
Pair of magnetic vice jaws Aluminium / fibre cover, smooth Jaw width 120 mm	967724 120
Pair of spare jaws with screws for "Heuer Front" Jaw width 120 mm	967405 120