

BROCKHAUS | HEUER

“Heuer-Front” bench vice, Jaw width: 160mm**Order data**

| | |
|--------------|---------------|
| Order number | 967350 160 |
| GTIN | 2050002047662 |
| Item class | 93Q |

Description**Version:****Made entirely of forged steel – guaranteed unbreakable.****Opens forward.** With forged pipe jaws underneath the normal jaws. Strong spindle with **two-start trapezoidal thread** for quick opening and closing of the jaws. Galvanised spindle wrench with riveted steel circlips. Spindle and guide tracks protected from dirt. Adjustable, double-sided Vee guide.

With reinforced anvil shoulder for shaping and compressing work.

Serrated surface-hardened jaws, not interchangeable.

Supplied with:

Fastening screws for attachment to the worktop.

Colour:Hammer-effect blue, **powder-coated.****Note:**

For suitable height adjuster see No. 967540.

Technical description

| | |
|-------------------|--------------------|
| Clamping depth | 100 mm |
| Jaw capacity | 225 mm |
| Weight | 27 kg |
| Opening direction | opens to the front |

| | |
|------------------------------------|-------------------|
| Material | Drop forged steel |
| Pipe jaws clamp pipes with outer Ø | 27 - 100 mm |
| Jaw width | 160 mm |
| Series | Heuer Front |
| exchangeable jaws | no |
| Type of product | Machinist's vice |

Accessories

| | |
|--|----------------|
| Pair of magnetic vice jaws Aluminium, Vee form Jaw width 160 mm | 967723 160 |
| Bench vice mounting plate, bamboo Size 300X250 | 967328 300X250 |
| Height adjuster for vices No. 967350 / 7360 / 7420 / 7430 suitable for vice size 160/180 | 967540 160/180 |
| Bench vice mounting plate | 967330 |
| Pair of magnetic vice jaws Aluminium / fibre cover, smooth Jaw width 160 mm | 967724 160 |
| Swivel base separate suitable for vice size 160/180 | 967390 160/180 |
| Pair of light metal vice jaws with spring clips Jaw width 160 mm | 967711 160 |
| Pair of magnetic vice jaws Aluminium, profiled Jaw width 160 mm | 967722 160 |