

**Bench vice, Jaw width: 140mm****Order data**

Order number	967310 140
GTIN	4045197694348
Item class	92H

Description**Version:**

Entirely forged from steel - guaranteed unbreakable.

Slides forward on opening. With forged pipe clamping jaws.

Milled case-hardened jaws Large capacity. Strong lead screw with trapezoidal thread. Spindle and guides protected from dirt. Adjustable guide; broad hardened anvil area.

Supplied with:

Fasteners for attachment to the workbench.

Note:

Suitable swivel base No. 967280 size 150.

Technical description

Opening direction	opens to the front
Weight	18 kg
Jaw capacity	200 mm
Clamping depth	100 mm
Material	Drop forged steel
Pipe jaws clamp pipes with outer Ø	3/4 – 3.1/2 in
Jaw width	140 mm

Type of product	Machinist's vice
-----------------	------------------

Accessories

Pair of magnetic vice jaws Aluminium, Vee form Jaw width 140 mm	967723 140
---	------------

Pair of magnetic vice jaws Aluminium / fibre cover, smooth Jaw width 140 mm	967724 140
---	------------

Pair of magnetic vice jaws Aluminium, profiled Jaw width 140 mm	967722 140
---	------------

Bench vice mounting plate, bamboo Size 300X250	967328 300X250
--	----------------

Pair of light metal vice jaws with spring clips Jaw width 140 mm	967711 140
--	------------

Bench vice mounting plate	967330
---------------------------	--------

Swivel base separate suitable for vice size 150	967280 150
---	------------