

**Bench vice, Jaw width: 100mm****Order data**

Order number	967420 100
GTIN	4045197694355
Item class	92H

Description**Version:**

Entirely of steel – guaranteed unbreakable. Slides forward on opening. With forged pipe clamping jaws underneath the normal jaws. Lead screw with trapezoidal thread, enclosed and protected from dirt. Double Vee form guide with adjustment facility. With anvil shoulder for light shaping and upsetting.

With serrated, hardened jaws (not exchangeable).

Supplied with:

Fasteners for attachment to the workbench.

Note:

For suitable height adjuster see No. 967540.

Technical description

Jaw capacity	100 mm
Opening direction	opens to the front
Clamping depth	50 mm
Weight	5 kg
Material	Drop forged steel
Pipe jaws clamp pipes with outer Ø	16 - 40 mm

Jaw width	100 mm
exchangeable jaws	no
Type of product	Machinist's vice

Accessories

Pair of magnetic vice jawsFelt, smooth Jaw width 100 mm	967726 100
Pair of magnetic vice jawsAluminium / fibre cover, smooth Jaw width 100 mm	967724 100
Pair of magnetic vice jawspolyurethane, Vee form Jaw width 100 mm	967729 100
Pair of magnetic vice jawspolyurethane, serrated Jaw width 100 mm	967728 100
Pair of magnetic vice jawsAluminium, Vee form Jaw width 100 mm	967723 100
Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Pair of magnetic vice jawsRubber, smooth Jaw width 100 mm	967727 100
Pair of magnetic vice jawsAluminium, profiled Jaw width 100 mm	967722 100
Pair of light metal vice jaws with spring clips Jaw width 100 mm	967711 100
Bench vice mounting plate	967330
Pair of magnetic vice jawsAluminium, smooth, standard Jaw width 100 mm	967721 100