

BROCKHAUS | HEUER

**“Heuer-Front” bench vice with swivel base, Jaw width: 120mm****Order data**

Order number	967370 120
GTIN	2050002047723
Item class	93Q

**Description****Version:****Made entirely of forged steel – guaranteed unbreakable.****Opens forward.** With forged pipe jaws underneath the normal jaws. Strong spindle with **two-start trapezoidal thread** for quick opening and closing of the jaws. Galvanised spindle wrench with riveted steel circlips. Spindle and guide tracks protected from dirt. Adjustable, double-sided Vee guide.

With reinforced anvil shoulder for shaping and compressing work.

Serrated surface-hardened jaws, not interchangeable.

Swivel base can be rotated continuously 360° and can be securely locked in any position.

**Supplied with:**

Fastening screws for attachment to the worktop.

**Colour:**Hammer-effect blue, **powder-coated.****Technical description**

Opening direction	opens to the front
Material	Drop forged steel
Jaw width	120 mm
Series	Heuer Front

exchangeable jaws	no
Type of product	Machinist's vice

---

## Accessories

Pair of magnetic vice jawsAluminium, profiled Jaw width 120 mm	967722 120
Pair of magnetic vice jawsAluminium / fibre cover, smooth Jaw width 120 mm	967724 120
Pair of light metal vice jaws with spring clips Jaw width 120 mm	967711 120
Bench vice mounting plate, bamboo Size 300X250	967328 300X250
Pair of magnetic vice jawsAluminium, Vee form Jaw width 120 mm	967723 120
Bench vice mounting plate	967330