

## Technician's vice with bench clamp, Jaw width: 50mm



### Order data

Order number	967590 50
GTIN	2050001741363
Item class	97G

### Description

#### Version:

The upper part can be rotated or swung to the most favourable operating position by means of a ball joint and can be locked by a clamping lever. The vice can be rotated additionally in **6°** steps up to 360°; and is therefore applicable as a low level clamp. Vice, bracket and screw on base are of light metal alloy, hammer finish enamelled. Enclosed steel thread spindle, jaws slide forwards on opening. With interchangeable plastic jaws.

### Technical description

Rotation range of ball joint	360 degrees
Jaw capacity	75 mm
Pivoting range of ball joint	90 degrees
Clamping depth	35 mm
Jaw width	50 mm
Clamping range	0 - 80 mm
exchangeable jaws	yes

Bench clamp included	yes
Type of product	Machinist's vice

---

## Accessories

Universal clamping device	967650
Pair of spare plastic jaws Jaw width 50 mm	967620 50