

**Technician's vice with bench clamp, Jaw width: 75mm****Order data**

Order number	967590 75
GTIN	2050001741561
Item class	97G

**Description****Version:**

The upper part can be rotated or swung to the most favourable operating position by means of a ball joint and can be locked by a clamping lever. The vice can be rotated additionally in **6°** steps up to 360°; and is therefore applicable as a low level clamp. Vice, bracket and screw on base are of light metal alloy, hammer finish enamelled. Enclosed steel thread spindle, jaws slide forwards on opening. With interchangeable steel jaws.

**Technical description**

Pivoting range of ball joint	90 degrees
Rotation range of ball joint	360 degrees
Clamping depth	50 mm
Jaw capacity	110 mm
Jaw width	75 mm
Clamping range	0 - 80 mm
exchangeable jaws	yes

Bench clamp included	yes
Type of product	Machinist's vice

---

## Accessories

Pair of spare plastic jaws Jaw width 75 mm	967620 75
Universal clamping device	967650