

Garant**Height adjuster for vice No. 967100 / 7110, suitable for vice size: 100****Order data**

| | |
|--------------|---------------|
| Order number | 967520 100 |
| GTIN | 4045197694461 |
| Item class | 91J |

Description**Version:**

Sturdy and very strong **forged parts** / steel design. Very smooth-running and precise guidance due to CNC-machined components. Extremely strong clamping by the special locking device. A built-in gas pressure spring ensures weight compensation during height adjustment of the vice. Quick clamping in any desired position by means of the **safety clamping lever**.

Advantage:

In conjunction with the height adjuster the vice can be **rotated by 360° without an additional swivel base** in order to bring the component into the best working position. The safety margin of 25 mm specified in DIN 31001 part 1 is kept during all height and angle adjustments.

Application:

For centimetre-accurate adjustment of the vice to the ideal working height (particularly important in training workshops and school workshops).

Suitable for:

Bench vices **GARANT No. 967100; 967110**.

Supplied with:

All fastening screws for attachment to the workbench.

Colour:

Silver-grey.

Technical description

| | |
|--------------------------------|-----------------|
| Weight | 10.3 kg |
| suitable for vice size | 100 |
| adjustable above workbench top | 93 - 335 mm |
| Height adjustment range | 242 mm |
| Type of product | Height adjuster |