

Technician's vice with screw-on base, Jaw width: 50mm



Order data

Order number	967600 50
GTIN	2050001741578
Item class	97G

Description

Version:

The upper part can be rotated or swung to the most favourable operating position by means of a ball joint and can be locked by a clamping lever. The vice can be rotated additionally in **6°** steps up to 360°; and is therefore applicable as a low level clamp. Vice, bracket and screw on base are of light metal alloy, hammer finish enamelled. Enclosed steel thread spindle, jaws slide forwards on opening. With interchangeable plastic jaws.

Technical description

Jaw capacity	75 mm
Rotation range of ball joint	360 degrees
Clamping depth	35 mm
Pivoting range of ball joint	90 degrees
Jaw width	50 mm
exchangeable jaws	yes
with screw-on base	yes
Type of product	Machinist's vice

Accessories

Pair of spare plastic jaws Jaw width 50 mm

967620 50

Universal clamping device

967650