

## Technician's vice with screw-on base, Jaw width: 75mm



### Order data

Order number	967600 75
GTIN	2050001741370
Item class	97G

### Description

#### Version:

The upper part can be rotated or swung to the most favourable operating position by means of a ball joint and can be locked by a clamping lever. The vice can be rotated additionally in **6°** steps up to 360°; and is therefore applicable as a low level clamp. Vice, bracket and screw on base are of light metal alloy, hammer finish enamelled. Enclosed steel thread spindle, jaws slide forwards on opening. With interchangeable steel jaws.

### Technical description

Rotation range of ball joint	360 degrees
Jaw capacity	110 mm
Pivoting range of ball joint	90 degrees
Clamping depth	50 mm
Jaw width	75 mm
exchangeable jaws	yes
with screw-on base	yes
Type of product	Machinist's vice

---

**Accessories**

Universal clamping device

967650

Pair of spare plastic jaws Jaw width 75 mm

967620 75