

**Garant****Height adjuster for vice No. 967100 / 7110, suitable for vice size: 140****Order data**

Order number	967520 140
GTIN	4045197694485
Item class	91J

**Description****Version:**

Sturdy and very strong **forged parts** / steel design. Very smooth-running and precise guidance due to CNC-machined components. Extremely strong clamping by the special locking device. A built-in gas pressure spring ensures weight compensation during height adjustment of the vice. Quick clamping in any desired position by means of the **safety clamping lever**.

**Advantage:**

In conjunction with the height adjuster the vice can be **rotated by 360° without an additional swivel base** in order to bring the component into the best working position. The safety margin of 25 mm specified in DIN 31001 part 1 is kept during all height and angle adjustments.

**Application:**

For centimetre-accurate adjustment of the vice to the ideal working height (particularly important in training workshops and school workshops).

**Suitable for:**

Bench vices **GARANT No. 967100; 967110**.

**Supplied with:**

All fastening screws for attachment to the workbench.

**Colour:**

Silver-grey.

## Technical description

suitable for vice size	140
Weight	11.6 kg
adjustable above workbench top	93 - 335 mm
Height adjustment range	242 mm
Type of product	Height adjuster