

Technician's vice with clamping block and bench clamp, Jaw width: 50mm**Order data**

Order number	967610 50
GTIN	2050001741387
Item class	97G

Description**Version:**

The upper part can be rotated or swung to the most favourable operating position by means of a ball joint and can be locked by a clamping lever. The vice can be rotated additionally in **6°** steps up to 360°; and is therefore applicable as a low level clamp. Vice, bracket and screw on base are of light metal alloy, hammer finish enamelled. Enclosed steel thread spindle, jaws slide forwards on opening.

With aluminium block jaws for clamping the most diverse workpiece shapes.

Technical description

Jaw capacity	75 mm
Clamping depth	35 mm
Pivoting range of ball joint	90 degrees
Rotation range of ball joint	360 degrees
Jaw width	50 mm
Clamping range	0 - 80 mm

exchangeable jaws	yes
with clamping block	yes
Bench clamp included	yes
Type of product	Machinist's vice

Accessories

Pair of spare aluminium clamping blocks Jaw width 50 mm	967630 50
Universal clamping device	967650
Pair of spare plastic clamping blocks Jaw width 50 mm	967635 50