



Pair of gloves HyFlex® 11-518, Glove size: 9



Order data

Order number	094478 9
GTIN	10076490478602
Item class	04P

Description

Version:

HyFlex® 11-518. Fine and flexible gloves with **light weight** of only 14 gm. Together with **high freedom of movement for the fingers** for less tiredness of the hand muscles when used for long periods. With **18 gauge knitted fabric** and Dyneema® diamond technology fibres. Particularly suitable for handling and assembly of extremely small sharp-edged components.

Version of the advertising text:

PU-coated cut-resistant gloves with **high dexterity**, optimum for working with sharp-edged components.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Accuracy of fit	very good
EN 388 tear propagation resistance	3
Heat protection	not available

Touch sensitivity	very good
Wet grip	good
Oil grip	good
Glove size	9
DMF-free	no
Breathability	good
Material of coating	PU
silicone-free	no
EN 388 cut resistance	3
EN 388 abrasion resistance	3
Series	HyFlex®
Type of glove	Multi-purpose gloves
Protection category	Category II
Contents	12
Glove characteristics	Suitable for allergy sufferers
Knitted technology	18G
EN 388	3X31B
Backing material	Nylon; Dyneema®
Coating	PU
Material	PU
Coating variant	The palms of the hands
Application range	Precision
Colour	blue
Weight	14 g
Length	210 mm
Application	reusable
Cut protection class	B
Type of product	Cut-resistant gloves

